



Digta Scan 404 **Digta Scan 407**

Perfect Organisation at the touch of a button

Digta Scan 404 – Digta Scan 407

Gathering and recording data.

By simply plugging the Digta Scan 404 into a dictation machine with scanner slot, you make your workflow just perfect.

The Digta Scan 407 product with retaining clip was specially developed for the Digta 7.

- Innovative plug-in barcode reader
- Fast and accurate method to index dictation
- Ideal way to reference patient and client files (as number or name)
- Easy to use ergonomic scanner
- Clear text display of barcode data in the display of the mobile dictation machines
- Reads all conventional 1 D-barcodes

www.grundig-gbs.com · info@grundig-gbs.com · Infoline: +49(0) 911-47 58-4

Your Grundig Business Systems Partner:




Just plug it in...



... and scan.

Operating controls



Funktionen

<i>Single functions</i>	<p>Barcode reader switch-on/switch-off (not with PC microphones)</p> <p>Barcode scan when creating a new dictation</p> <p>Visual and acoustic signal of the scanned barcode</p> <p>Pilot indicator for scanned characters on the display for ex. EAN 13 for numeric display or code 39 to show the client's name in clear letters on the display (not with PC micro-phones)</p> <p>Unequivocal indexing by automatic saving of the scanned barcode with the dictation</p> <p>Display in the "Topic" (up to 32 characters) or "Dictation Data" (more than 32 characters) field of the dictation label's accompanying note.</p> <p>Programming for several barcode symbologies</p> <p>Fast, full proof barcode recognition when programming only one barcode symbology</p> <p>Barcode reader reset to factory settings</p> <p>Transfer for barcode data as Windows keyboard entry (only with PC microphones)</p>
<i>Connection to the dictation machine</i>	Plug-in connection via multimedia/secure digital card slot – card reader lock and release catch
<i>Compatible barcode types</i>	<p>UPC-A, UPC-E, UPC-E1</p> <p>EAN-8, EAN-13, Bookland EAN</p> <p>USS-128, UCC/EAN-128, ISBT 128</p> <p>Code 39, Code 93</p> <p>Interleaved 2 of 5, Discrete 2 of 5</p> <p>Codabar</p> <p>MSI Plessey</p>
<i>Barcode length</i>	No limitation
<i>Supplied with barcode type (default setting)</i>	EAN-13
<i>Permanent connection to dictation machine</i>	<p>Digta Scan 404: Available from customer service (on request)</p> <p>Digta Scan 407: Retaining clip on the casing's back</p>

Technical Data

<i>Scanning process</i>	One-dimensional scanning with laser beam
<i>Laser class</i>	Class 1, no hazard for skin and eyes
<i>Scanning distance</i>	Up to 9.84 inch. (25 cm)
<i>Scanning angle</i>	30°, ergonomic handling
<i>Dimensions</i>	<p>Overall: width approx. 1.93 inch. (49 mm), height approx. 2.91 inch. (74 mm), depth approx. 0.94 inch. (24 mm)</p> <p>Plugged-in: width approx. 1.93 inch. (49 mm), height approx. 1.69 inch. (43 mm), depth approx. 0.94 inch. (24 mm)</p>
<i>storage Temperature</i>	-20°C (-4°F) to +70°C (158°F)
<i>operation Temperature</i>	-5°C (+23°F) to +35°C (95°F)
<i>Weight</i>	Approximately 0.81 ounce (23 g)
<i>Case colour</i>	black
<i>Suitable for</i>	Digta Scan 404: Digta 420, Digta 422, Digta SonicMic II, Digta CordEx, Digta 4015 DS
<i>Digta Scan 407</i>	Digta Scan 407: Digta 7

Scope of delivery

Digta Scan 404/407

Please make sure to choose only genuine accessories from Grundig. Product liability and warranty service are provided only in this case. The use of non-Grundig accessories or those which are not recommended and approved by Grundig automatically void any warranty claims towards Grundig.

Grundig Business Systems GmbH, Emmericher Str. 17, D-90411 Nürnberg, Email: info@grundig-gbs.com, Internet: www.grundig-gbs.com. Printed in Germany.

We reserve the right to make technical changes and improvements.
Order number: HNE 5114 04/2015